

TASCAM

DR-100MKIII Professional Handheld Recorder

Tested Media List (as of 2020-09-15)

The listed media were tested successfully with this model.

Over time, these specific media may become unavailable. At that time, it would be best to contact the CF/SD/USB media manufacturer directly and have them suggest the model with the most similar specifications that is currently available which remains within the maximum capacity limit.

Manufacturer	Model	Part No.	Capacity
Tascam	Tascam SD Card	TSQD-32A	32 GB
SanDisk	Extreme Pro SD UHS-II	SDSDXPK-064G-JNJIP	64 GB
		SDSDXPK-032G-JNJIP	32 GB
	Extreme SDHC/SDXC UHS-I (U3, Class 10)	SDSDXVF-128G-JNJIP*	128 GB
		SDSDXVE-064G-JNJIP*	64 GB
		SDSDXNE-016G-JNJIP*	16 GB
	Extreme Pro SDHC UHS-I	SDSDXPA-032G-JU3*	32 GB
		SDSDXL-016G-JU3*	16 GB
	Extreme Pro SDHC UHS-I	SDSDXPA-032G-J35N*	32 GB
	Extreme Plus SDHC UHS-I	SDSDXS-032G-J35P*	32 GB
	Extreme SDHC UHS-I	SDSDXL-032G-J35*	32 GB
	Ultra Plus SDHC UHS-I	SDSDUM-016G-J01*	32 GB
	Extreme Pro SDHC UHS-I (Class 10)	SDSDXPA-128G-JU3	128 GB
		SDSDXPA-064G-JU3	64 GB
		SDSDXPA-016G-JU3	16 GB
	Extreme SDHC UHS-I (Class 10)	SDSDXL-064G-JU3	64 GB
		SSDSXL-032G-JU3	32 GB
	Standard SDHC (Class 4)	SDSDB-008G-J01	8 GB
	Extreme Pro SDHC (Class10/UHS-II)	SDSDXPB-032G-J35	32 GB
		SDSDXPB-016G-J35	16 GB
	Extreme Pro SDHC (Class 10/UHS-I)	SDSDXPA-016G-J35N	16 GB
	Extreme Plus SDHC UHS-I (Class 10)	SDSDXS-016G-J35P*	16 GB
	Extreme SDHC UHS-I (Class 10)	SDSDXL-016G-J35*	16 GB
	Ultra Plus SDHC UHS-I	SDSDUP-016G-J35	16 GB
SDSDUP-008G-J35		8 GB	
Panasonic	SDUC series (UHS-I / Class10)	RP-SDUC32GJK	32 GB
Sony	SDXC/SDHC UHS-II SF-G Series	SF-G32T	32 GB
		SF-G64T	64 GB
		SF-G128T	128 GB
	SDXC/SDHC UHS-I (SF-UY3 Series)	SF-128UY3*	128 GB
		SF-64UY3	64 GB
		SF-32UY3*	32 GB
		SF-16UY3*	16 GB
	SDHC UHS-I	SF-8UY2	8 GB
	Toshiba	SDHC/SDXC SDBR48N Series	SDBR48N32G
Exceria SDHC/SDXC (SD-FU Series)		SD-FU032G	32 GB

		SD-FU016G	16 GB
	Exceria Pro SDHC/SDXC (SD-KU Series)	SD-KU032G	32 GB
		SD-KU016G	16 GB
Transcend		SDXC/SDHC UHS-I Speed (Class 3)	TS32GSDU3X

*The performance of the media may be degraded significantly if used repeatedly. Use the unit's ERASE FORMAT function in this case prior to further recording.

Design and specifications subject to change without notice.

Page last modified: 2020-09-15 16:21:04 UTC

TEAC Europe GmbH

Bahnstrasse 12

65205 Wiesbaden

Germany

Tel: +49 611 7158-0

Share this page:

© 2003–2020 TEAC Europe GmbH · TEAC Corporation · All rights reserved.